



# KC20TN, SERVIT POST Mechanical Connector, Cable to Flat, Tin Plated

By Burndy  
Catalog # [KC20TN](#)



Tin plated; #10 - #5 AWG Stranded Copper or #10 - #4 AWG Solid Copper; 5/16" Stud; 165 in-lb recommended torque.

## General

Catalog Number	KC20TN
Material	Bronze, Leaded, Commercial
Plated	Y
Plating Type	Tin - Electro Plated
Stud Installation Torque inch pounds	180 LBS/in
Trade Name	SERVIT POST™
Type	KC and K2C Series
UPC	781810087985
UPC 12 Digit	7818100879855

## Dimensions

Dimension - B Length inch	0.41 in
Dimension - Body Width inch	0.50 in
Dimension - D inch	0.63 in
Dimension - Height inch	0.86 in
Dimension - L Length Overall mm	36 mm
Dimension - Length Overall inch	1.42 in
Dimension - Nut Width inch	0.69 in
Dimension - P inch	0.22 in

## Conductor Related

Conductor - Copper Solid Size	10 AWG;9 AWG;8 AWG;7 AWG;6 AWG;5 AWG;4 AWG
Conductor - Copper Solid Size Range	4 AWG-10 AWG
Conductor - Copper Str Size	10 AWG;9 AWG;8 AWG;7 AWG;6 AWG;5 AWG
Conductor - Copper Str Size Range	5 AWG-10 AWG
Physical Attribute - Number of Conductors Accommodated Total	1

## Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	Yes

## Logistics

Carton Quantity	50
Minimum Pack Quantity	1
Pallet Quantity	19800

## Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR\\_KC\\_Lineart](#)
- [Sales Drawings - 10020944](#)
- [Specifications - KC20TN](#)



A Hubbell brand