



KC23NSP, SERVIT POST Mechanical Connector, Cable to Flat

By Burndy
Catalog # [KC23NSP](#)



Mechanical Connector; Cable to Flat; Nut Torque: 275 in-lbs;
Stud Torque: 280 in-lbs; supplied with split lock washer and nut.

General

Catalog Number	KC23NSP
Material	Bronze, Leaded, Commercial
Plated	N
Plating Type	Unplated
Stud Installation Torque inch pounds	280 LBS/in
Trade Name	SERVIT POST™
Type	KC and K2C Series
UPC	781810310120
UPC 12 Digit	7818103101200

Dimensions

Dimension - B Length inch	0.46 in
Dimension - Body Width inch	0.62 in
Dimension - D inch	0.63 in
Dimension - Height inch	1.05 in
Dimension - L Length Overall mm	42 mm
Dimension - Length Overall inch	1.67 in
Dimension - Nut Width inch	0.81 in
Dimension - P inch	0.32 in

Conductor Related

Conductor - Copper Solid Size	10 AWG;9 AWG;8 AWG;7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG
Conductor - Copper Solid Size Range	10 AWG-1 AWG
Conductor - Copper Str Size	8 AWG;7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG
Conductor - Copper Str Size Range	8 AWG-2 AWG
Physical Attribute - Number of Conductors Accommodated Total	1

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Carton Quantity	50
Minimum Pack Quantity	1
Pallet Quantity	19800

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - sd055917](#)
- [Specifications - KC23NSP](#)



A Hubbell brand