



KC28B1G16, SERVIT POST Mechanical Connector, Cable to Flat

By Burndy
Catalog # [KC28B1G16](#)



Mechanical Connector; Cable to Flat; 3/8"-16 Stud.

General

| | |
|--------------------------------------|----------------------|
| Catalog Number | KC28B1G16 |
| Material | Bronze Alloy, Leaded |
| Plated | N |
| Plating Type | Unplated |
| Stud Installation Torque inch pounds | 280 LBS/in |
| Trade Name | SERVIT POST™ |
| Type | KC and K2C Series |
| UPC | 781810276181 |
| UPC 12 Digit | 7818102761811 |

Dimensions

| | |
|---------------------------------|---------|
| Dimension - B Length inch | 1.25 in |
| Dimension - Body Width inch | 1.18 in |
| Dimension - Height inch | 1.94 in |
| Dimension - L Length Overall mm | 88 mm |
| Dimension - Length Overall inch | 3.45 in |
| Dimension - Nut Width inch | 1.35 in |
| Dimension - P inch | 0.55 in |

Conductor Related

| | |
|--|---------------------------------------|
| Conductor - Copper Solid Size | 1 AWG;1/0 AWG;2/0 AWG;3/0 AWG;4/0 AWG |
| Conductor - Copper Solid Size Range | 1 AWG-4/0 AWG |
| Conductor - Copper Str Size | 1 AWG;1/0 ;2/0 AWG;3/0 AWG;4/0 AWG |
| Conductor - Copper Str Size Range | 1 AWG-4/0 AWG |
| Physical Attribute - Number of Conductors Accommodated Total | 1 |

Certifications And Compliance

| | |
|---|-------|
| Certification - CSA Approved | No |
| Certification - ETL | No |
| Certification - UL Listed Direct Burial | Yes |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Industry Standard(s) | UL467 |
| Standards - Industry Standards Met | UL467 |
| Standards - RoHS Compliance Status | EX |
| UL Listed | Yes |

Logistics

| | |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
|-----------------------|---|

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Specifications - KC28B1G16](#)