



KC34W, SERVIT POST Mechanical Connector, Cable to Flat, Tin Plated

By Burndy
Catalog # [KC34W](#)



Mechanical Connector; Cable to Flat; Accommodates: 3/0 Stranded - 500 kcmil; 3/4" Stud; Hot Tin Dipped.

General

Material Plated	Copper Alloy, Cast Y
Plating Type	Tin - Hot Dipped
Stud Installation Torque inch pounds	1050 LBS/in
Trade Name	SERVIT POST™
Type	KC and K2C Series
UPC 12 Digit	0

Dimensions

Dimension - B Length inch	0.99 in
Dimension - Body Width inch	1.62 in
Dimension - Height inch	2.38 in
Dimension - L Length Overall mm	92 mm
Dimension - Length Overall inch	3.62 in
Dimension - Nut Width inch	2.00 in
Dimension - P inch	0.85 in

Conductor Related

Conductor - Copper Str Size	1 AWG;1/0 ;2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil;300 kcmil
-----------------------------	--

Physical Attribute - Number of Conductors Accommodated Total 1

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Product Cross Section Image\(s\) - BUR_KC_Lineart](#)
[Sales Drawings - 10020944](#)



A proud member of the Hubbell Family.