



KIT11G27, Seamless Terminal #10 AWG 3/8" Stud w/ Hex Nuts

By Burndy
Catalog # [KIT11G27](#)



Packaged Kit of YAD1038 and Hex Nuts

*Representative Image

General

Catalog Number	KIT11G27
Connector Type	Small Terminal Kit
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Long
Insulation	Y
Insulation Type	Nylon
Material	Copper
Physical Attribute - Number of Holes	1
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	N
Type	Small Terminal Kit
UPC	781810146033
UPC 12 Digit	7818101460333

Dimensions

Dimension - Hole Size fraction	2/5
Dimension - Hole Size inch	0.40 in
Dimension - Length Overall inch	1.08 in
Dimension - Pad Width inch	0.58 in
Dimension - Stud Size inch	3/8
Dimension - Thread Size	-
Dimension - Z (inch)	0.44 in

Conductor Related

Conductor - Copper Str Size	12 AWG;10 AWG
Conductor - Copper Str Size Range	12 AWG-10 AWG
Conductor Type	<ul style="list-style-type: none">• CU C Solid-Size• CU C Str-Size

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	N
Certification - cULus	N
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	100
Minimum Pack Quantity	100

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Specifications - KIT11G27](#)



A Hubbell brand