


KK6A31U8, AL Universal Terminal, 6 Conductors, #6 AWG-350 kcmil, 8-Hole, Dual Rated

By Burndy
Catalog # [KK6A31U8](#)



6 Conductors #6 AWG - 350 kcmil; Dual Rated.

Features

- Dual rated panelboard lugs constructed from high strength extruded aluminum alloy , electro tin-plated to provide low contact resistance

General

Catalog Number	KK6A31U8
Connector Type	Parallel Set-Screw
Construction Material - Main	Aluminum
EU RoHS Indicator	Contact Manufacturer
Finish Type	Clear Plate
Material	Aluminum
Number of Holes	8
Physical Attribute - Number of Holes	8
Plated	Y
Plating Type	Clear plated
Sub Brand	Universal Terminals
Type	KK6A-U
UPC	781810666630

Dimensions

Dimension - Bolt Size fraction	9/16
Dimension - Height inch	1.5 in
Dimension - Height mm	38.1 mm
Dimension - L Length Overall mm	171 mm
Dimension - Length Overall inch	6.75 in
Dimension - Stud Size fraction	9/16

Conductor Related

Conductor - AL Str Size Range	12 Str. - 350 Kcmil
Conductor - Copper Str Size Range	12 Str. - 350 Kcmil
Conductor Size	6 AWG-350 KCMIL
Conductor Type	<ul style="list-style-type: none"> • CU C Str-Size • AL C Str-Size
Number Of Wires	6
Number of Conductors	6

Certifications And Compliance

Buy American Compliant	Contact Manufacturer
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

Logistics

Carton Quantity	12
Minimum Pack Quantity	1

Product Assets

- [Catalogs - BURNDY Master Catalog - Section A - Mechanical](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 50040505](#)
- [Specifications - KK6A31U8](#)