



## KLU35TP, Copper Terminal, Offset Tongue, 1 Hole, 14 AWG (Sol)-6 AWG (Str), #10 Stud, 1 Screw, Tin Plated

By Burndy  
Catalog # KLU35TP



SCRULUG™ Mechanical Offset Tongue Terminal for Copper Cable; 1-Hole; Accommodates: #14 Sol - #6 Str; 3/16" Hardware Slot/Robertson; Installation Torque: 35 in-lbs; Wire Strip Length: 5/8".

### Features

- Range-taking design reduces SKUs required in inventory
- High conductivity copper alloy for long lasting reliable contact
- Compact design, easy to install
- Slot Robertson screw, hex head, hex socket bolt require no special installation tools

### General

Catalog Number	KLU35TP
Connector Type	Pressure Bar
Hardware Type	1/4 UNF Slotted SetScrew
Installation Torque	35
Recommended in-lb	
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Number of Screws	1
Physical Attribute - Screw Type	Slot
Plated	Y
Plating Type	Tin
Trade Name	SCRULUG™
Type	Bolted Lugs & Terminals
UPC	781810352557

### Dimensions

Dimension - B Length fraction	7/16 in
Dimension - B Length inch	0.43 in
Dimension - Bolt Size fraction	#10
Dimension - Hole Size inch	0.20 in
Dimension - Hole Size mm	5 mm
Dimension - L Length Overall mm	31 mm
Dimension - Length Overall inch	1.24 in
Dimension - N inch	0.22 in
Dimension - Pad Width inch	0.39 in
Dimension - Screw Size inch	1/4
Dimension - Strip Length inch	5/8
Dimension - Stud Size inch	#10

### Conductor Related

Conductor - Copper Solid Size	14 AWG;13 AWG;12 AWG;11 AWG;10 AWG;9 AWG;8 AWG;7 AWG;6 AWG
Conductor - Copper Solid Size Range	14 AWG-6 AWG
Conductor - Copper Str Size	14 AWG;12 AWG;10 AWG;9 AWG;8 AWG;7 AWG;6 AWG
Conductor - Copper Str Size Range	14 AWG-6 AWG
Conductor Size	14-6 AWG
Conductor Type	<ul style="list-style-type: none"><li>• CU C Solid-Size</li><li>• CU C Str-Size</li></ul>

## Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	No
Certification - UL Recognized	No
Certification - cULus	Yes
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Carton Quantity	500
Minimum Pack Quantity	5000
Pallet Quantity	18560

## Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section A - Mechanical](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - sd207469-01](#)
- [Specifications - KLU35TP](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
BRDY-KLU35TP-SPEC-EN | REV 8/2024