



**KLU70TP, Mechanical Offset
Tongue, #8 Sol-#2 AWG Str, 1-Hole,
1/4" Stud, 1 Screw, Tin Plated**

By Burndy
Catalog # [KLU70TP](#)

SCRULUG™ Mechanical Offset Tongue Terminal for Copper
Cable; 1-Hole; Accommodates: #8 - #2; 5/16" UNF Slotted Screw;
1/4" Stud Hole; Torque: 40 in-lbs; 3/4" Length.



Features

- Range-taking design reduces SKUs required in inventory
- High conductivity copper alloy for long lasting reliable contact
- Compact design, easy to install
- Slot Robertson screw, hex head, hex socket bolt require no special installation tools

General

Catalog Number	KLU70TP
Connector Type	Pressure Bar
Hardware Type	5/16 UNF Slotted SetScrew
Installation Torque	40
Recommended in-lb	
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Number of Screws	1
Physical Attribute - Screw Type	Slot
Plated	Y
Plating Type	Tin
Trade Name	SCRULUG™
Type	Bolted Lugs & Terminals
UPC	781810352601

Dimensions

Dimension - B Length fraction	1/2 in
Dimension - B Length inch	0.50 in
Dimension - Bolt Size fraction	1/4
Dimension - Hole Size inch	0.26 in
Dimension - Hole Size mm	7 mm
Dimension - L Length Overall mm	39 mm
Dimension - Length Overall inch	1.55 in
Dimension - N inch	0.25 in
Dimension - Pad Width inch	0.47 in
Dimension - Screw Size inch	5/16
Dimension - Strip Length inch	3/4

Dimension - Stud Size inch 1/4

Conductor Related

Conductor - Copper Solid Size	8 AWG;7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG
Conductor - Copper Solid Size Range	8 AWG-2 AWG
Conductor - Copper Str Size	8 AWG;7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG
Conductor - Copper Str Size Range	8 AWG-2 AWG
Conductor Size	8-2 AWG
Conductor Type	<ul style="list-style-type: none">• CU C Solid-Size• CU C Str-Size

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	No
Certification - UL Recognized	No
Certification - cULus	Yes
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	500
Minimum Pack Quantity	3000

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Catalogs - BURNDY Master Catalog - Section A - Mechanical](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - sd207469-01](#)
[Specifications - KLU70TP](#)

