



KPA4CHEXGR, Mechanical Pressure Bar Style Copper Lug, 1-Hole, #4 Str-14 Sol, 1/4" Stud

By Burndy

Catalog # [KPA4CHEXGR](#)



Cu Alloy SCRULUG Terminal, W/Grounding Hexagonal Screw, 1 Hole, #4 Str. - #14 Sol., 1/4" Stud.

General

Catalog Number	KPA4CHEXGR
Connector Type	Terminal
Installation Torque	35
Recommended in-lb	
Material	Copper Alloy
Number Of Ports	1
Physical Attribute - Number of Holes	1
Physical Attribute - Number of Screws	1
Plated	Y
Plating Type	Tin Plated
Temperature Rating	194
Trade Name	SCRULUG™
Type	Bolted Lugs & Terminals
UPC	781810172445
UPC 12 Digit	7818101724455

Dimensions

Dimension - Height inch	0.94
Dimension - Height mm	0 mm
Dimension - Hole Size inch	0.27
Dimension - Length Overall inch	1.2
Dimension - N inch	0.3
Dimension - Pad Width inch	0.5
Weight	0.03 lb

Electrical Ratings

Rating - Minimum Voltage 600

Conductor Related

Conductor - Copper Str Navy Size	#23 AWG;#30 AWG;#40 AWG
Conductor - Copper Str Size Range	#4 AWG to #14 AWG;16 mm ² to 2.5 mm ²

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Carton Quantity	100
Minimum Pack Quantity	1
Pallet Quantity	59400

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 50055474](#)
- [Specifications - KPA4CHEXGR](#)