

KPA8CCAN, Pressure Bar Style Copper Lug, #14 Sol-#8 Str, 1-Hole

By Burndy
Catalog # [KPA8CCAN](#)

Cu Alloy SCRULUG Terminal, 1 Hole, #14 Sol. - #8 Str.



General

Catalog Number	KPA8CCAN
Connector Type	Terminal
Material	Copper
Plated	N
Plating Type	Unplated
Temperature Rating	194
Trade Name	SCRULUG™
Type	Bolted Lugs & Terminals
UPC	781810432488
UPC 12 Digit	7818104324888

Dimensions

Dimension - Height mm	0 mm
-----------------------	------

Electrical Ratings

Rating - Minimum Voltage	600
--------------------------	-----

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Specifications - KPA8CCAN](#)