

KPA8CUPG10, Copper Terminal, 1-Hole, #14 AWG Sol-6 AWG Str, 1 Screw, Green Screw

By Burndy
Catalog # [KPA8CUPG10](#)



Copper Terminal, 1 Hole, 14 AWG (Sol)-6 AWG (Str), #10 Stud, 1 Screw; Green Screw.

Features

- High copper alloy terminal (unplated) for joining a wide range of cable to equipment pads or terminal blocks
- Tongue and body are 1-piece design, pressure bar equalizes pressure over the conductor and prevents the screw from cutting into the cable

General

Catalog Number	KPA8CUPG10
Connector Type	Terminal
Installation Torque	35
Recommended in-lb	
Material	Copper
Plated	Y
Plating Type	Tin
Trade Name	SCRULUG™
Type	Bolted Lugs & Terminals
UPC	781810043981

Dimensions

Dimension - Height inch	0.81 in
Dimension - Hole Size inch	0.20 in
Dimension - Hole Size mm	5.1 mm
Dimension - L Length Overall mm	26.4 mm
Dimension - Length Overall inch	1.04 in
Dimension - Stud Size inch	#10
Dimension - Width inch	0.38 in
Dimension - Width mm	9.4 mm

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	UI
UL Listed	Yes

Logistics

Minimum Pack Quantity	2000
-----------------------	------

Product Assets

- [3D Models - KPA8CUPG10_MODEL-PDF](#)
- [3D Models - KPA8CUPG10_MODEL-IGES](#)
- [3D Models - KPA8CUPG10_MODEL-STEP](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 30022847](#)
- [Specifications - KPA8CUPG10](#)