



KS17SV, Split Bolt Connector, Run: #8 Str-#6 Sol, Tap: #14-#6 Str, Silver Plated

By Burndy
Catalog # [KS17SV](#)

Cu Alloy SERVIT Split Bolt, #8 Str. - #6 Sol.(Run), #14 - #6 Str.
(Tap), Silver Plated.



General

Connector Type	Split Bolt
Material	Copper
Plated	Y
Plating Type	Silver
Trade Name	SERVIT®
UPC	781810067697
UPC 12 Digit	7818100676977

Dimensions

Dimension - Length Overall inch	1.14
Width	0.45 in

Conductor Related

Conductor - Copper Solid Run	6 AWG
Conductor - Copper Solid Tap	6 AWG
Conductor - Copper Str Run Range	8 STR - 6 STR
Conductor - Copper Str Tap Range	8 STR - 6 STR

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	100
Minimum Pack Quantity	1
Pallet Quantity	89100

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - sd078561](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-KS17SV-SPEC-EN | REV 1/2024