



KS20, Split Bolt Connector, Run/Tap: #8 AWG Str-#4 AWG Sol

By Burndy
Catalog # [KS20](#)

Copper Split Bolt, Cu: 8 AWG (Str)-4 AWG (Sol) (Run & Tap),Length:1.20.



Application

For Direct Burial Applications In Earth Or Concrete, Copper

General

EU RoHS Indicator	Yes
Sub Brand	SERVIT
Type	KS, Compact
UPC	781810012000

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	100
Minimum Pack Quantity	100
Pallet Quantity	99000

Product Assets

- [3D Models - KS20_MODEL-IGES](#)
- [3D Models - KS20_MODEL-PDF](#)
- [3D Models - KS20_MODEL-STEP](#)
- [Catalogs - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Sales Drawings - SD..078561-01](#)
- [Sell Sheets - SERVIT® Split-bolt Connectors](#)



A proud member of the Hubbell Family.