



KS20TN, Split Bolt Connector, Run: #8-#4 AWG, Tap: #14-#4 AWG, Tin Plated

By Burndy
Catalog # [KS20TN](#)



Cu Alloy SERVIT Split Bolt, #8 - #4 AWG(Run), #14 - #4 AWG(Tap), Tin Plated.

General

Catalog Number	KS20TN
Connector Type	Split Bolt
Material	Copper
Plated	Y
Plating Type	Tin Plated
Trade Name	SERVIT®
UPC	781810129081
UPC 12 Digit	7818101290811

Dimensions

Dimension - Length Overall inch	1.2
Width	0.51 in

Conductor Related

Conductor - Copper Solid Run	4 AWG
Conductor - Copper Solid Tap	4 AWG
Conductor - Copper Str Run Range	8 STR - 4 STR
Conductor - Copper Str Tap Range	8 STR - 4 STR
Conductor Type	<ul style="list-style-type: none">• CU C Solid-Run• CU C Str-Run• CU Weld C Str-Run• CU C Solid-Tap• CU C Str-Tap• CU Weld C Str-Tap

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL486D
Standards - Industry Standards Met	UL486D
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	100
Minimum Pack Quantity	1
Pallet Quantity	29000

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - sd078561](#)
[Specifications - KS20TN](#)



A Hubbell brand