



KS22, Split Bolt Connector, Run/Tap: #8 AWG Str-6 AWG Sol

By Burndy
Catalog # [KS22](#)

Copper Split Bolt, Cu: 8 AWG (Str)-6 AWG (Sol) (Run & Tap),Length:1.50.



Application

For Direct Burial Applications In Earth Or Concrete, Copper

General

| | |
|-------------------|--------------|
| EU RoHS Indicator | Yes |
| Sub Brand | SERVIT |
| Type | KS, Compact |
| UPC | 781810012505 |

Certifications and Compliance

| | |
|------------------------------------|-----|
| Certification - CSA Approved | No |
| Certification - ETL | No |
| Standards - RoHS Compliance Status | CM |
| UL Listed | Yes |

Logistics

| | |
|-----------------------|-------|
| Carton Quantity | 100 |
| Minimum Pack Quantity | 1 |
| Pallet Quantity | 52800 |

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - SD..078561-01](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-KS22-SPEC-EN | REV 1/2024