



**KS23TN, Split Bolt Connector, Run:
#6-#1 AWG, Tap: #14-1 AWG, Tin
Plated**

By Burndy
Catalog # [KS23TN](#)

Cu Alloy SERVIT Split Bolt, #6 - #1 AWG(Run), #14 - #1
AWG(Tap), Tin Plated.

General

Catalog Number	KS23TN
Connector Type	Split Bolt
Material	Copper
Plated	Y
Plating Type	Tin Plated
Trade Name	SERVIT®
UPC	781810054253
UPC 12 Digit	7818100542533

- CU Weld C Str-Run
- CU C Solid-Tap
- CU C Str-Tap
- CU Weld C Str-Tap

Certifications And Compliance

Certification - CSA Approved	No
Industry Standard(s)	UL486D
Standards - Industry Standards	UL486D
Met	
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

Logistics

Carton Quantity	100
Minimum Pack Quantity	1
Pallet Quantity	17400

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - sd078561](#)
[Specifications - KS23TN](#)

Dimensions

Dimension - Length Overall inch	1.54
Width	0.62 in

Conductor Related

Conductor - Copper Solid Run	1 AWG
Conductor - Copper Solid Tap	1 AWG
Conductor - Copper Str Run Range	6 STR - 2 STR
Conductor - Copper Str Tap Range	6 STR - 2 STR
Conductor Type	<ul style="list-style-type: none">• CU C Solid-Run• CU C Str-Run