



## KS25TN, Split Bolt Connector, Run: #4-1/0 AWG, Tap: #14-1/0 AWG, Tin Plated

By Burndy  
Catalog # [KS25TN](#)



Cu Alloy SERVIT Split Bolt, #4 - 1/0 (Run), #14 - 1/0 AWG(Tap),  
Tin Plated.

### General

Catalog Number	KS25TN
Connector Type	Split Bolt
Installation Torque	385 in
Recommended in-lb	
Material	Copper
Plated	Y
Plating Type	Tin Plated
Trade Name	SERVIT®
UPC	781810349243
UPC 12 Digit	7818103492433

### Dimensions

Dimension - Cross Flats inch	.94 in
Dimension - L Length Overall mm	45 mm
Dimension - Length Overall inch	1.77
Dimension - Width fraction	73/100 in
Dimension - Width inch	0.73 in
Dimension - Width mm	19 mm
Width	0.73 in

### Conductor Related

Conductor - Copper Solid Run	2/0 AWG
Conductor - Copper Solid Tap	2/0 AWG
Conductor - Copper Str Run Range	4 STR - 1/0 STR
Conductor - Copper Str Tap Range	4 STR - 1/0 STR
Conductor Type	<ul style="list-style-type: none"><li>• CU C Solid-Run</li><li>• CU C Str-Run</li><li>• CU Weld C Solid-Run</li><li>• CU Weld C Str-Run</li><li>• CU C Str-Tap</li><li>• CU Weld C Solid-Tap</li><li>• CU Weld C Str-Tap</li><li>• CU C Solid-Tap</li></ul>

### Certifications And Compliance

Certification - UL Listed Direct Burial	Yes
Industry Standard(s)	<ul style="list-style-type: none"><li>• UL 486A</li><li>• UL486B</li></ul>
Standards - Industry Standards Met	<ul style="list-style-type: none"><li>• UL 486A</li><li>• UL486B</li></ul>
Standards - RoHS Compliance Status	CM

### Logistics

Carton Quantity	25
Minimum Pack Quantity	1
Pallet Quantity	14850

### Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Product Cross Section Image\(s\) - BUR\\_KS\\_Lineart\\_BW](#)  
[Sales Drawings - SD..078561-01](#)  
[Specifications - KS25TN](#)

