



KS26NK, Split Bolt Connector, Run/Tap: #2 AWG-2/0 AWG Str, Nickel Plated

By Burndy
Catalog # [KS26NK](#)



Copper Split Bolt, Cu: 2 AWG-2/0 AWG (Str) (Run & Tap); Nickel Plated.

General

| | |
|---------------------|---------------|
| Catalog Number | KS26NK |
| Connector Type | Split Bolt |
| Installation Torque | 385 in |
| Recommended in-lb | |
| Material | Copper |
| Plated | Y |
| Plating Type | Nickel |
| Trade Name | SERVIT® |
| UPC | 781810354797 |
| UPC 12 Digit | 7818103547977 |

Dimensions

| | |
|---------------------------------|----------|
| Dimension - B Length inch | .90 in |
| Dimension - Cross Flats inch | 1.05 in |
| Dimension - L Length Overall mm | 49 mm |
| Dimension - Length Overall inch | 1.94 in |
| Dimension - Width fraction | 41/50 in |
| Dimension - Width inch | 0.82 in |
| Dimension - Width mm | 21 mm |

Conductor Related

| | |
|----------------|---|
| Conductor Type | <ul style="list-style-type: none">• CU C Solid-Run• CU C Str-Run• CU Weld C Solid-Run• CU Weld C Str-Run• CU C Str-Tap• CU Weld C Solid-Tap• CU Weld C Str-Tap• CU C Solid-Tap |
|----------------|---|

Certifications And Compliance

| | |
|---|--|
| Certification - CSA Approved | No |
| Certification - ETL | No |
| Certification - UL Listed Direct Burial | Yes |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Industry Standard(s) | <ul style="list-style-type: none">• UL 486A• UL486B |
| Standards - Industry Standards Met | <ul style="list-style-type: none">• UL 486A• UL486B |
| Standards - RoHS Compliance Status | CM |
| UL Listed | No |

Logistics

| | |
|-----------------------|-------|
| Carton Quantity | 25 |
| Minimum Pack Quantity | 1 |
| Pallet Quantity | 11600 |

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_KS_Lineart_BW](#)
[Specifications - KS26NK](#)