



KS26TN, Split Bolt Connector, Run: #2-2/0 AWG, Tap: #14-2/0 AWG, Tin Plated

By Burndy
Catalog # [KS26TN](#)

Cu Alloy SERVIT Split Bolt, #2 - 2/0 AWG(Run), #14 - 2/0 AWG(Tap), Tin Plated.



General

Connector Type	Split Bolt
Material	Copper
Plated	Y
Plating Type	Tin Plated
Trade Name	SERVIT®
UPC	781810088463
UPC 12 Digit	7818100884633

Dimensions

Dimension - Length Overall inch	1.94
Width	0.82 in

Conductor Related

Conductor - Copper Solid Run	3/0 AWG
Conductor - Copper Solid Tap	3/0 AWG
Conductor - Copper Str Run Range	2 STR - 2/0 STR
Conductor - Copper Str Tap Range	2 STR - 2/0 STR
Conductor Type	<ul style="list-style-type: none">• CU C Solid-Run• CU C Str-Run• CU Weld C Str-Run• CU C Solid-Tap• CU C Str-Tap• CU Weld C Str-Tap

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL486D
Standards - Industry Standards Met	UL486D
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	25
Minimum Pack Quantity	1
Pallet Quantity	7425

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - sd078561](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-KS26TN-SPEC-EN | REV 5/2024