

KS28, Split Bolt Connector, Run/Tap: #1-4/0 AWG

By Burndy
Catalog # KS28



Copper Split Bolt, Cu: 1-4/0 AWG (Run & Tap).

General

Catalog Number	KS28
Connector Type	Split Bolt
Installation Torque	650 in
Recommended in-lb	
Material	Copper
Plated	N
Plating Type	Unplated
Trade Name	SERVIT®
UPC	781810422007
UPC 12 Digit	7818104220077

Dimensions

Dimension - L Length Overall mm	53 mm
Dimension - Length Overall inch	2.46
Dimension - Width inch	1.17 in
Dimension - Width mm	30 mm
Width	1.18 in

Conductor Related

Conductor - Copper Solid Run	1 AWG;1/0 AWG;2/0 AWG;3/0 AWG;4/0 AWG
Conductor - Copper Solid Run Range	1 AWG - 4/0 AWG
Conductor - Copper Solid Tap	1 AWG;1/0 AWG;2/0 AWG;3/0 AWG;4/0 AWG
Conductor - Copper Solid Tap Range	1 AWG - 4/0 AWG
Conductor - Copper Str Run	1 AWG;1/0 ;2/0 AWG;3/0 AWG;4/0 AWG
Conductor - Copper Str Run Range	1 STR - 4/0 STR
Conductor - Copper Str Tap	1 AWG;1/0 ;2/0 AWG;3/0 AWG;4/0 AWG
Conductor - Copper Str Tap Range	1 STR - 4/0 STR

Conductor Type

- CU C Solid-Run
- CU C Str-Run
- CU Weld C Solid-Run
- CU Weld C Str-Run
- CU C Str-Tap
- CU Weld C Solid-Tap
- CU Weld C Str-Tap
- CU C Solid-Tap

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	<ul style="list-style-type: none"> • UL 486A • UL486B
Standards - Industry Standards Met	<ul style="list-style-type: none"> • UL 486A • UL486B
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

- [3D Models - KS28_MODEL-IGES](#)
- [3D Models - KS28_MODEL-PDF](#)
- [3D Models - KS28_MODEL-STEP](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_KS_Lineart_BW](#)
- [Sales Drawings - 10102446](#)
- [Specifications - KS28](#)