



## KS29G4, Split Bolt Connector, Run: #1 AWG Str-250 kcmil, Tap: #8 AWG-250 kcmil

By Burndy  
Catalog # [KS29G4](#)



Cu Alloy SERVIT Split Bolt, #1 AWG - 250 kcmil(Run), #8 AWG - 250 kcmil(Tap).

### General

Catalog Number	KS29G4
Connector Type	Split Bolt
Plated	Y
Plating Type	Tin
Trade Name	SERVIT®
UPC	781810054314
UPC 12 Digit	7818100543144

### Conductor Related

Conductor Type	<ul style="list-style-type: none"><li>• CU C Solid-Run</li><li>• CU C Str-Run</li><li>• CU Weld C Str-Run</li><li>• CU C Solid-Tap</li><li>• CU C Str-Tap</li><li>• CU Weld C Str-Tap</li></ul>
----------------	---

### Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL486D
Standards - Industry Standards Met	UL486D
Standards - RoHS Compliance Status	EX
UL Listed	No

### Logistics

Minimum Pack Quantity	34
-----------------------	----

### Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Sales Drawings - sd078561](#)  
[Specifications - KS29G4](#)