



## KS29TN, Split Bolt Connector, Run: #1 Str-4/0 Sol, Tap: #8 Str-250 kcmil, Tin Plated

By Burndy  
Catalog # [KS29TN](#)

Cu Alloy SERVIT Split Bolt, 4/0 Sol. - #1 Str.(Run), 250 kcmil - #8 Str.(Tap), Tin Plated.



### General

Catalog Number	KS29TN
Connector Type	Split Bolt
Material	Copper
Plated	Y
Plating Type	Tin Plated
Trade Name	SERVIT®
UPC	781810094105
UPC 12 Digit	7818100941055

### Dimensions

Dimension - Length Overall inch	2.25
Width	1 in

### Conductor Related

Conductor - Copper Solid Run	4/0 AWG
Conductor - Copper Solid Tap	4/0 AWG
Conductor - Copper Str Run Range	1 STR - 250 KCMIL
Conductor - Copper Str Tap Range	1 STR - 250 KCMIL

### Certifications And Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	CM

### Logistics

Minimum Pack Quantity	65
-----------------------	----

### Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Sales Drawings - sd078561](#)  
[Specifications - KS29TN](#)