



# KS34, Split Bolt Connector, Run/Tap: 2/0 AWG Str-500 kcmil

By Burndy  
Catalog # [KS34](#)

Copper Split Bolt, Cu: 2/0 AWG (Str)-500 kcmil (Run & Tap).



## Application

For Direct Burial Cables

## General

EU RoHS Indicator	Yes
Material	Copper
Plated	N
Plating Type	Unplated
Sub Brand	SERVIT
Trade Name	SERVIT
UPC	781810014509
UPC 12 Digit	7818100145099

## Dimensions

Dimension - B Length fraction	1-31/100 in
Dimension - B Length inch	1.31 in
Dimension - Cross Flats inch	1.82 in
Dimension - L Length Overall mm	71 mm
Dimension - Length Overall inch	2.79 in
Dimension - Width fraction	1-12/25 in
Dimension - Width inch	1.48 in
Dimension - Width mm	38 mm

## Conductor Related

Conductor - Copper Solid Run	2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil;300 kcmil;350 kcmil;400 kcmil;450 kcmil;500 kcmil
Conductor - Copper Solid Run Range	2/0 AWG-500 kcmil
Conductor - Copper Solid Tap	2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil;300 kcmil;350 kcmil;400 kcmil;450 kcmil;500 kcmil
Conductor - Copper Solid Tap Range	2/0 AWG-500 kcmil
Conductor - Copper Str Run	2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil;300 kcmil;350 kcmil;400 kcmil;450 kcmil;500 kcmil
Conductor - Copper Str Run Range	2/0 AWG-500 kcmil
Conductor - Copper Str Tap	2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil;300 kcmil;350 kcmil;400 kcmil;450 kcmil;500 kcmil
Conductor - Copper Str Tap Range	2/0 AWG-500 kcmil
Conductor - CopperWeld Str Run	19 #6
Conductor - CopperWeld Str Run Range	19 #6
Conductor - CopperWeld Str Tap	19 #6
Conductor - CopperWeld Str Tap Range	19 #6
Conductor - Rebar Size	6
Conductor - Rebar Size Range	6
Conductor Type	<ul style="list-style-type: none"> <li>• CU C Solid-Run</li> <li>• CU C Str-Run</li> <li>• CU Weld C Solid-Run</li> <li>• CU Weld C Str-Run</li> <li>• CU C Str-Tap</li> <li>• CU Weld C Solid-Tap</li> <li>• CU Weld C Str-Tap</li> <li>• CU C Solid-Tap</li> </ul>

## Certifications and Compliance

Certification - CSA Approved No

Certification - ETL	No
Certification - UL Listed Direct Burial	Y
Certification - UL Recognized	N
Certification - cULus	N
Standards - RoHS Compliance Status	EX
UL Listed	Yes

**Logistics**

Minimum Pack Quantity	1
-----------------------	---

**Product Assets**

- [3D Models - KS34\\_MODEL-PDF](#)
- [3D Models - KS34\\_MODEL-IGES](#)
- [3D Models - KS34\\_MODEL-STEP](#)
- [Catalogs - Communications Catalog \(CA12042E\)](#)
- [Catalogs - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Sales Drawings - SD..078561-01](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
BRDY-KS34-SPEC-EN | REV 1/2024