



KS90, Split Bolt Connector, Run/Tap: #12-10 AWG Str

By Burndy
Catalog # KS90



Copper Split Bolt, Cu: 12-10 AWG (Str) (Run & Tap).

Application

For Direct Burial Cables

General

Catalog Number	KS90
Connector Type	Split Bolt
EU RoHS Indicator	Yes
Installation Torque	80 in
Recommended in-lb	
Material	Copper
Plated	N
Plating Type	Unplated
Sub Brand	SERVIT
Trade Name	SERVIT®
Type	KS
UPC	781810015254
UPC 12 Digit	7818100152544

Dimensions

Dimension - B Length fraction	9/20 in
Dimension - B Length inch	.45 in
Dimension - Cross Flats inch	.50 in
Dimension - L Length Overall mm	22 mm
Dimension - Length Overall inch	0.85
Dimension - Width fraction	19/50 in
Dimension - Width inch	0.38 in
Dimension - Width mm	10 mm
Width	0.38 in

Conductor Related

Conductor - Copper Solid Run	8 AWG
Conductor - Copper Solid Run Range	10 AWG-12 AWG
Conductor - Copper Solid Tap	8 AWG
Conductor - Copper Solid Tap Range	16 AWG-10 AWG
Conductor - Copper Str Run	12 AWG;10 AWG
Conductor - Copper Str Run Range	12 STR. 10 STR.
Conductor - Copper Str Tap	16 AWG;14 AWG;12 AWG;10 AWG
Conductor - Copper Str Tap Range	16 STR.
Conductor - CopperWeld Solid Run	#10
Conductor - CopperWeld Solid Run Range	#10
Conductor - CopperWeld Solid Tap	#10
Conductor - CopperWeld Solid Tap Range	#10
Conductor Type	<ul style="list-style-type: none">• CU C Solid-Run• CU C Str-Run• CU Weld C Solid-Run• CU Weld C Str-Run• CU C Str-Tap• CU Weld C Solid-Tap• CU Weld C Str-Tap• CU C Solid-Tap

Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	<ul style="list-style-type: none">• UL 486A• UL486B
Standards - Industry Standards Met	<ul style="list-style-type: none">• UL 486A• UL486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	100
Minimum Pack Quantity	1
Pallet Quantity	99000

Product Assets

[3D Models - KS90_MODEL-PDF](#)
[3D Models - KS90_MODEL-IGES](#)
[3D Models - KS90_MODEL-STEP](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Catalogs - BURNDY Master Catalog - Section A - Mechanical](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_KS_Lineart_BW](#)
[Sales Drawings - SD..078561-01](#)
[Sell Sheets - SERVIT® Split-bolt Connectors](#)
[Specifications - KS90](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRDY-KS90-SPEC-EN | REV 8/2024