



KSSB28U, QIKSHEAR™ Shear Bolt Splice, 2/0-4/0 AWG

By Burndy
Catalog # [KSSB28U](#)

QIKSHEAR™ Shear Bolt Splice, 2/0-4/0 AWG, 3/8 socket



Features

- No Tooling or Die Investment Required, no crimp tools necessary
- Dual Rated AL9CU for use with both copper and aluminum conductor
- cULus Listed Wire Connector to UL486A-486B
- Up to 35kV voltage rating
- Tin Plated aluminum connectors and bolts reduce galvanic corrosion and oxide build up
- Range-taking capabilities on most sizes

General

UPC 621945658912

Dimensions

Length 4.50 in

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Installation Manuals - Shear Bolt Mechanical Connector](#)
[Installation Instructions](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-KSSB28U-SPEC-EN | REV 1/2024