



## KSSB31U, QIKSHEAR™ Shear Bolt Splice, 250-350 kcmil

By Burndy  
Catalog # KSSB31U



QIKSHEAR™ Shear Bolt Splice, 250-350 kcmil, 3/8 socket

### Features

- No Tooling or Die Investment Required, no crimp tools necessary
- Dual Rated AL9CU for use with both copper and aluminum conductor
- cULus Listed Wire Connector to UL486A-486B
- Up to 35kV voltage rating
- Tin Plated aluminum connectors and bolts reduce galvanic corrosion and oxide build up
- Range-taking capabilities on most sizes

### General

Catalog Number KSSB31U

UPC 621945658929

### Dimensions

Length 5 in

### Product Assets

[Catalogs - BURNDY Master Catalog - Section A - Mechanical](#)  
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Installation Manuals - Shear Bolt Mechanical Connector](#)  
[Installation Instructions](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Sales Drawings - 50109586](#)  
[Specifications - KSSB31U](#)