



KSSB39U, QIKSHEAR™ Shear Bolt Splice, 600-750 kcmil

By Burndy
Catalog # [KSSB39U](#)



QIKSHEAR™ Shear Bolt Splice, 600-750 kcmil, 3/8 socket

Features

- No Tooling or Die Investment Required, no crimp tools necessary
- Dual Rated AL9CU for use with both copper and aluminum conductor
- cULus Listed Wire Connector to UL486A-486B
- Up to 35kV voltage rating
- Tin Plated aluminum connectors and bolts reduce galvanic corrosion and oxide build up
- Range-taking capabilities on most sizes

General

Catalog Number KSSB39U
UPC 621945658936

Dimensions

Length 7 in

Logistics

Carton Quantity 20

Product Assets

[Catalogs - BURNDY Master Catalog - Section A - Mechanical](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Installation Manuals - Shear Bolt Mechanical Connector](#)
[Installation Instructions](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - 50109586](#)
[Specifications - KSSB39U](#)
[Test Documents - GCRE23-02-01](#)