



KSSB45U, QIKSHEAR™ Shear Bolt Splice, 1250 kcmil

By Burndy
Catalog # [KSSB45U](#)



QIKSHEAR™ Shear Bolt Splice, 1250 kcmil, 3/8 socket

Features

- No Tooling or Die Investment Required, no crimp tools necessary
- Dual Rated AL9CU for use with both copper and aluminum conductor
- cULus Listed Wire Connector to UL486A-486B
- Up to 35kV voltage rating
- Tin Plated aluminum connectors and bolts reduce galvanic corrosion and oxide build up
- Range-taking capabilities on most sizes

General

Catalog Number KSSB45U

UPC 621945658943

Dimensions

Length 7.25 in

Product Assets

[Catalogs - BURNDY Master Catalog - Section A - Mechanical](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - 50109586](#)
[Sell Sheets - Shear Bolt Mechanical Connectors, 1-Hole, 2-Hole, Splices](#)
[Specifications - KSSB45U](#)