



## KSU17, Split Bolt Connector with Spacer, Tin Plated

By Burndy  
Catalog # [KSU17](#)

Tin-plated, high strength copper alloy SERVIT with spacer. Spacer separates dissimilar conductors and provides long contact length.



### Application

For All Combinations Of Copper, Aluminum, ACSR, AAAC, 5005, And Steel

### General

Catalog Number	KSU17
Connector Type	Split Bolt
EU RoHS Indicator	Yes
Installation Torque	165 LBS/in
Recommended in-lb	
Material	Copper
Plated	Y
Plating Type	Tin Plated
Sub Brand	UNIVERSAL SERVIT
Trade Name	SERVIT®
Type	KSU, Universal
UPC	781810035009
UPC 12 Digit	7818100350099

### Dimensions

Dimension - Cross Flats inch	.62 in
Dimension - L Length Overall mm	23 mm
Dimension - Length Overall inch	1.14
Dimension - Width inch	0.42 in
Dimension - Width mm	11 mm
Width	0.42 in

## Conductor Related

Conductor - AAAC 5005 Run	30.58 (7) kcmil
Conductor - AAAC 5005 Run Range	30.58 (7) kcmil
Conductor - AAAC 5005 Tap	30.58 (7) kcmil
Conductor - AAAC 5005 Tap Range	30.58 (7) kcmil
Conductor - AAAC 6201 Run	30.58 (7) kcmil
Conductor - AAAC 6201 Run Range	30.58 (7) kcmil
Conductor - AAAC 6201 Tap	30.58 (7) kcmil
Conductor - AAAC 6201 Tap Range	30.58 (7) kcmil
Conductor - ACSR Str Run	8 (6-1)
Conductor - ACSR Str Run Range	8 AWG
Conductor - ACSR Str Tap	8 (6-1)
Conductor - ACSR Str Tap Range	8 AWG
Conductor - AL Str Run	8 AWG;6 AWG
Conductor - AL Str Run Range	12 STR. 6 SOL.
Conductor - AL Str Tap	8 AWG;6 AWG
Conductor - AL Str Tap Range	12 STR. 6 SOL.
Conductor - Copper Solid Run	12 AWG;11 AWG;10 AWG;9 AWG;8 AWG;7 AWG;6 AWG
Conductor - Copper Solid Run Range	12 AWG-6 AWG
Conductor - Copper Solid Tap	12 AWG;11 AWG;10 AWG;9 AWG;8 AWG;7 AWG;6 AWG
Conductor - Copper Solid Tap Range	12 AWG-6 AWG
Conductor - Copper Str Run	10 AWG;9 AWG;8 AWG;7 AWG;6 AWG;5 AWG;4 AWG
Conductor - Copper Str Run Range	12 STR. 6 SOL.
Conductor - Copper Str Tap	10 AWG;9 AWG;8 AWG;7 AWG;6 AWG;5 AWG;4 AWG
Conductor - Copper Str Tap Range	12 STR. 6 SOL.
Conductor - Galvanized Steel Str Size	5/32 (7) in
Conductor - Galvanized Steel Str Size Range	5/32 (7) in
Conductor Type	<ul style="list-style-type: none"><li>• CU C Solid-Run</li><li>• CU C Str-Run</li><li>• AL C Str-Run</li><li>• AAAC C 5005-Run</li><li>• AAAC C 6201-Run</li><li>• ACSR C Str-Run</li><li>• CU C Solid-Tap</li><li>• CU C Str-Tap</li><li>• AL C Str-Tap</li><li>• AAAC C 5005-Tap</li><li>• AAAC C 6201-Tap</li><li>• ACSR C Str-Tap</li><li>• GAL Steel C Str-Size</li></ul>

## Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	No
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

## Logistics

Carton Quantity	100
Minimum Pack Quantity	1
Pallet Quantity	29700

## Product Assets

[3D Models - KSU17\\_MODEL-PDF](#)  
[3D Models - KSU17\\_MODEL-STEP](#)  
[3D Models - KSU17\\_MODEL-IGES](#)  
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Catalogs - BURNDY Master Catalog - Section A - Mechanical](#)  
[Customer Notices - Prop 65 Notice](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Product Cross Section Image\(s\) - BUR\\_KSU\\_UNIV\\_SERVIT\\_LineArt](#)  
[Sales Drawings - SD..041343-01](#)  
[Specifications - KSU17](#)



A Hubbell brand