

KSU26, Split Bolt Connector with Spacer. Tin Plated

By Burndy
Catalog # KSU26



Tin-plated, high strength copper alloy SERVIT with spacer. Spacer separates dissimilar conductors and provides long contact length that prevents high pressure point contacts between run and tap conductors, 1.90 IN L.

Features

- Tin-plated, high strength copper alloy with spacer
- Spacer separates dissimilar conductors and provides long contact length preventing high pressure point contacts between run and tap conductors

Application

For All Combinations Of Copper, Aluminum, ACSR, AAAC, 5005, And Steel

General

Catalog Number	KSU26
Connector Type	Split Bolt
EU RoHS Indicator	Yes
Installation Torque	385
Recommended in-lb	
Material	Copper
Plated	Y
Plating Type	Tin Plated
Sub Brand	UNIVERSAL SERVIT
Trade Name	SERVIT®
Type	KSU, Universal
UPC	781810036600
UPC 12 Digit	7818100366000

Dimensions

Dimension - Cross Flats inch	1.04 in
Dimension - L Length Overall mm	49 mm
Dimension - Length Overall inch	1.95
Dimension - Width inch	0.79 in
Dimension - Width mm	20 mm
Width	0.79 in

Conductor Related

Conductor - AAAC 5005 Run	123.3 (7) kcmil
Conductor - AAAC 5005 Run Range	123.3 (7) kcmil

Conductor - AAAC 5005 Tap	30.58 (7) kcmil;48.69 (7) kcmil;77.47 (7) kcmil;123.3 (7) kcmil
Conductor - AAAC 5005 Tap Range	30.58 (7) kcmil-123.3 (7) kcmil
Conductor - AAAC 6201 Run	123.3 (7) kcmil
Conductor - AAAC 6201 Run Range	123.3 (7) kcmil
Conductor - AAAC 6201 Tap	30.58 (7) kcmil;48.69 (7) kcmil;77.47 (7) kcmil;123.3 (7) kcmil
Conductor - AAAC 6201 Tap Range	30.58 (7) kcmil-123.3 (7) kcmil
Conductor - ACSR Str Run	1 (6/1) Robin AWG;1/0 (6/1) Raven AWG
Conductor - ACSR Str Run Range	1 AWG - 1/0 AWG
Conductor - ACSR Str Tap	6 (6/1) Turkey AWG;5 (6/1) Thrush AWG;4 (6/1) Swan AWG;4 (7/1) Swanate AWG;3 (6/1) Swallow AWG;2 (6/1) Sparrow AWG;2 (7/1) Sparate AWG;1 (6/1) Robin AWG;1/0 (6/1) Raven AWG
Conductor - ACSR Str Tap Range	6 AWG - 1/0 AWG
Conductor - AL Str Run	2 AWG;1 AWG;1/0 AWG;2/0 AWG
Conductor - AL Str Run Range	2 AWG - 2/0 AWG
Conductor - AL Str Tap	8 AWG;6 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 AWG;2/0 AWG
Conductor - AL Str Tap Range	8 AWG - 2/0 AWG
Conductor - Copper Solid Run	22
Conductor - Copper Solid Run Range	22
Conductor - Copper Str Run	2 AWG;1 AWG;1/0 ;2/0 AWG
Conductor - Copper Str Run Range	2 AWG - 2/0 AWG
Conductor - Copper Str Tap	8 AWG;7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 ;2/0 AWG

Conductor - Copper Str Tap Range	8 AWG - 2/0 AWG
Conductor - Galvanized Steel Str Size	7/16 (7) in
Conductor - Galvanized Steel Str Size Range	7/16 (7) in
Conductor Type	<ul style="list-style-type: none"> • CU C Solid-Run • CU C Str-Run • AL C Str-Run • AAAC C 5005-Run • AAAC C 6201-Run • ACSR C Str-Run • CU C Solid-Tap • CU C Str-Tap • AL C Str-Tap • AAAC C 5005-Tap • AAAC C 6201-Tap • ACSR C Str-Tap • GAL Steel C Str-Size

Certification - CSA Approved	No
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

Logistics

Carton Quantity	25
Minimum Pack Quantity	1
Pallet Quantity	5800

Product Assets

- [3D Models - KSU26_MODEL-IGES](#)
- [3D Models - KSU26_MODEL-STEP](#)
- [3D Models - KSU26_MODEL-PDF](#)
- [Catalogs - BURNDY Master Catalog - Section A - Mechanical](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_KSU_UNIV_SERVIT_LineArt](#)
- [Sales Drawings - SD..041343-01](#)
- [Specifications - KSU26](#)

Certifications And Compliance

Buy American Compliant	Yes
------------------------	-----



A Hubbell brand