



KSU28, Split Bolt Connector with Spacer, Run/Tap: Cu/Al #1-4/0 AWG

By Burndy
Catalog # [KSU28](#)



Copper Split Bolt w/ Spacer, (Cu & Al): 1-4/0 AWG (Run & Tap).

General

Catalog Number	KSU28
Connector Type	Split Bolt
Material	Copper
Plated	Y
Plating Type	Tin Plated
Trade Name	SERVIT®
UPC	781810424162
UPC 12 Digit	7818104241622

- CU C Solid-Tap
- CU C Str-Tap
- AL C Str-Tap
- AAAC C 5005-Tap
- AAAC C 6201-Tap
- ACSR C Str-Tap
- GAL Steel C Str-Size

Dimensions

Dimension - Length Overall inch	2.46
Width	1.18 in

Conductor Related

Conductor - Copper Solid Run Range	1 AWG - 4/0 AWG
Conductor - Copper Solid Tap Range	1 AWG - 4/0 AWG
Conductor - Copper Str Run Range	1 STR - 4/0 STR
Conductor - Copper Str Tap Range	1 STR - 4/0 STR
Conductor Type	<ul style="list-style-type: none">• CU C Solid-Run• CU C Str-Run• AL C Str-Run• AAAC C 5005-Run• AAAC C 6201-Run• ACSR C Str-Run

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	25
-----------------------	----

Product Assets

- [3D Models - KSU28_MODEL-IGES](#)
- [3D Models - KSU28_MODEL-PDF](#)
- [3D Models - KSU28_MODEL-STEP](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_KSU_UNIV_SERVIT_LineArt](#)
- [Sales Drawings - 10104971](#)
- [Specifications - KSU28](#)