



KSU29, Split Bolt Connector with Spacer, Tin Plated

By Burndy
Catalog # [KSU29](#)

Tin-plated, high strength copper alloy SERVIT with spacer. Spacer separates dissimilar conductors and provides long contact length that prevents high pressure point contacts between run and tap conductors, 2.50 IN L.



Application

For All Combinations Of Copper, Aluminum, ACSR, AAAC, 5005, And Steel

General

Catalog Number	KSU29
EU RoHS Indicator	Yes
Material	Copper
Plated	Y
Plating Type	Tin Plated
Sub Brand	UNIVERSAL SERVIT
Trade Name	SERVIT®
Type	KSU, Universal
UPC	781810036853

Dimensions

Dimension - Length Overall inch	2.66
Width	1.22 in

Conductor Related

Conductor - ACSR Str Run Range	2/0 AWG - 4/0 AWG
Conductor - ACSR Str Tap Range	6 AWG - 4/0 AWG
Conductor - AL Str Run Range	1 AWG - 250 KCMIL
Conductor - AL Str Tap Range	8 AWG - 250 KCMIL
Conductor - Copper Str Run Range	1 AWG - 250 KCMIL
Conductor - Copper Str Tap Range	8 AWG - 250 KCMIL

Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	No
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Catalogs - BURNDY Master Catalog - Section A - Mechanical](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - SD..041343-01](#)
[Specifications - KSU29](#)