



KVS28G6, 2-piece OKLIP Service Connector for heavy duty applications, Run: 1/0-4/0 AWG Str, Tap: #10-4/0 AWG Str

By Burndy
Catalog # KVS28G6



Cast Cu Alloy Mechanical Service Connector, 1/0 - 4/0 AWG STR (Run), #10 - 4/0 AWG STR (Tap).

General

Catalog Number	KVS28G6
Material	Copper
Plated	N
Plating Type	Unplated
Trade Name	OKLIP™
UPC	781810145098
UPC 12 Digit	7818101450988

Conductor Related

Conductor Type	<ul style="list-style-type: none">• CU C Str-Run• CU C Str-Tap• CU Weld C Solid-Run• CU Weld C Solid-Tap
----------------	---

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL486C
Standards - Industry Standards Met	UL486C
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - SC..052062-01](#)
[Specifications - KVS28G6](#)



A Hubbell brand