



KVS28G7, 2-piece OKLIP Service Connector for heavy duty applications, Run: 1/0-4/0 Str, Tap: #10 Str-4/0 Str

By Burndy
Catalog # [KVS28G7](#)

Cast Cu Alloy Service Connector, 1/0 - 4/0 Str.(Run), #10 Str. - 4/0 Str. (Tap).

General

Catalog Number	KVS28G7
Material	Copper
Plated	N
Plating Type	Unplated
Trade Name	OKLIP™
UPC	781810098288
UPC 12 Digit	7818100982888

Dimensions

Dimension - Height mm	0 mm
-----------------------	------

Conductor Related

Conductor Type	<ul style="list-style-type: none">• CU C Str-Run• CU C Str-Tap• CU Weld C Solid-Run• CU Weld C Solid-Tap
----------------	---

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL486C
Standards - Industry Standards Met	UL486C
Standards - RoHS Compliance	CM
Status	
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - SC..052062-01](#)
- [Specifications - KVS28G7](#)