



KVS28TN, 2-piece OKLIP Service Connector for heavy duty applications, Run: 1/0-4/0 Str, Tap: #10-4/0 Str, Tin Plated

By Burndy
Catalog # [KVS28TN](#)



Cast Cu Alloy Service Connector, 1/0 - 4/0 Str. (Run), #10 - 4/0 Str.(Tap), Tin Plated.

General

| | |
|----------------|---------------|
| Catalog Number | KVS28TN |
| Material | Copper |
| Plated | Y |
| Plating Type | Tin |
| Trade Name | OKLIP™ |
| UPC | 781810503041 |
| UPC 12 Digit | 7818105030411 |

Dimensions

| | |
|----------------------------|----------|
| Dimension - Height inch | 1.82 in |
| Dimension - Height mm | 46.23 mm |
| Dimension - Stud Size inch | 3/8 in |
| Dimension - Width inch | 1.67 in |

Conductor Related

| | |
|----------------------------------|---------------------|
| Conductor - Copper Str Run Range | 1/0 str. - 4/0 str. |
|----------------------------------|---------------------|

| | |
|----------------------------------|--------------------|
| Conductor - Copper Str Tap Range | 10 str. - 4/0 str. |
|----------------------------------|--------------------|

Certifications And Compliance

| | |
|------------------------------------|----|
| Certification - CSA Approved | No |
| Certification - ETL | No |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Standards - RoHS Compliance Status | UI |
| UL Listed | No |

Logistics

| | |
|-----------------------|-----|
| Minimum Pack Quantity | 100 |
|-----------------------|-----|

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - SC..052062-01](#)
[Specifications - KVS28TN](#)