



KVS31A, 2-piece OKLIP Service Connector for heavy duty applications, Run: 250-350 kcmil

By Burndy
Catalog # [KVS31A](#)

High-conductivity, non-copper bearing aluminum alloy connector. Spacer bar separates dissimilar conductors. Intended for heavy duty applications, conductor range, Run Cu and Al :250-350.



Application

For All Combinations Of Copper, Aluminum, ACSR, AAAC And 5005

General

EU RoHS Indicator	Yes
Sub Brand	OKLIP
Type	KVS
UPC	781810072004

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - sd063282-01](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-KVS31A-SPEC-EN | REV 5/2024