



KVS31AG12, 2-piece OKLIP Service Connector for heavy duty applications, AL alloy

By Burndy
Catalog # [KVS31AG12](#)

Cast Al Alloy Mechanical OKLIP, 250 - 350 kcmil Cu/AAC, 4/0 AWG - 336.4 kcmil Al/ACSR(Run), #6 Str. - 350 kcmil Cu/AAC, #6 AWG - 336.4 kcmil Al/ACSR(Tap).



General

Catalog Number	KVS31AG12
Material	Aluminum
Plated	N
Plating Type	Unplated
Trade Name	OKLIP™
UPC	781810096765
UPC 12 Digit	7818100967655

Conductor Related

Conductor Type	<ul style="list-style-type: none">• AL C Str-Run• CU C Str-Run• ACSR C Cmpt-Run• AAAC C 5005-Run• AAAC C 6201-Run• AL C Str-Tap• CU C Str-Tap• ACSR C Cmpt-Tap• AAAC C 5005-Tap• AAAC C 6201-Tap
----------------	---

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_kvsala](#)
[Sales Drawings - sd063282-01](#)
[Specifications - KVS31AG12](#)