



KVS31G14, 2-piece OKLIP Service Connector for heavy duty applications, Run: 250-350 kcmil, TapL #10-250 kcmil

By Burndy
Catalog # [KVS31G14](#)



Cast Cu Alloy Service Connector, 250 - 350 kcmil(Run), 250 kcmil - #10 Str.(Tap).

General

Catalog Number	KVS31G14
Material	Copper
Plated	N
Plating Type	Unplated
Trade Name	OKLIP™
UPC	781810113943
UPC 12 Digit	7818101139433

Dimensions

Dimension - Height mm	0 mm
-----------------------	------

Conductor Related

Conductor Type	<ul style="list-style-type: none">• CU C Str-Run• CU C Str-Tap• CU Weld C Solid-Run• CU Weld C Solid-Tap
----------------	---

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL486C
Standards - Industry Standards	UL486C
Met	
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - SC..052062-01](#)
- [Specifications - KVS31G14](#)