



KVS34AG19, 2-piece OKLIP Service Connector for heavy duty applications

By Burndy
Catalog # [KVS34AG19](#)

Cast Al Alloy Mech OKLIP, 400-500 kcmil Cu/AAC, 336.4-397.5 kcmil Al/ACSR(Run), #5 Str.-500 kcmil Cu, #5 Str.-397.5 kcmil Al/ACSR, #4 AWG-500 kcmil AAC(Tap).



General

Catalog Number	KVS34AG19
Material	Copper
Plated	N
Plating Type	Unplated
Trade Name	OKLIP™
UPC	781810496800
UPC 12 Digit	7818104968000

Conductor Related

Conductor - ACSR Str Run Range	336.4 kcmil - 397.5 kcmil
Conductor - ACSR Str Tap Range	5 ACSR - 397.5 kcmil
Conductor - AL Str Run Range	400 kcmil- 500 kcmil
Conductor - AL Str Tap Range	4 str.- 500 kcmil
Conductor - Copper Str Run Range	400 kcmil- 500 kcmil
Conductor - Copper Str Tap Range	5 str. - 500 kcmil

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

Logistics

Minimum Pack Quantity	100
-----------------------	-----

Product Assets

- [3D Models - KVS34AG19_MODEL-PDF](#)
- [3D Models - KVS34AG19_MODEL-IGES](#)
- [3D Models - KVS34AG19_MODEL-STEP](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 10112062](#)
- [Specifications - KVS34AG19](#)