



KVS40A, 2-piece OKLIP Service Connector for heavy duty applications

By Burndy
Catalog # [KVS40A](#)

High-conductivity, non-copper bearing aluminum alloy connector. Spacer bar separates dissimilar conductors. Intended for heavy duty applications, conductor range, Run Cu and Al :400-800.



Application

For All Combinations Of Copper, Aluminum, ACSR, AAAC And 5005

General

| | |
|-------------------|--------------|
| EU RoHS Indicator | Yes |
| Sub Brand | OKLIP |
| Type | KVS |
| UPC | 781810073506 |

Certifications And Compliance

| | |
|------------------------------------|----|
| Certification - CSA Approved | No |
| Certification - ETL | No |
| Standards - RoHS Compliance Status | CM |
| UL Listed | No |

Logistics

| | |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
|-----------------------|---|

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - sd063282-01](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-KVS40A-SPEC-EN | REV 5/2024