



## **KVSU34G3, Mechanical Connector with Spacer Bar**

By Burndy  
Catalog # [KVSU34G3](#)

Cast Cu Alloy Universal Service Connector, Silicon Bronze H/W,.



## General

Catalog Number	KVSU34G3
Material	Copper
Plated	Y
Plating Type	Tin
Trade Name	OKLIP™
UPC	781810500033
UPC 12 Digit	7818105000333

## Dimensions

Dimension - Length Overall inch	1.34 in
Dimension - Stud Size inch	1/2 in
Dimension - Width inch	2.20 in

## Conductor Related

Conductor - ACSR Str Run Range	336.4 kcmil-397.5 kcmil
Conductor - ACSR Str Tap Range	5 ACSR-397.5 kcmil
Conductor - AL Str Run Range	400 kcmil- 500 kcmil
Conductor - AL Str Tap Range	4 str.- 500 kcmil
Conductor - Copper Str Run Range	400 kcmil- 500 kcmil
Conductor - Copper Str Tap Range	4 str. - 500 kcmil
Conductor - Galvanized Steel Str Run Range	3/4 in - 3/4 in
Conductor - Galvanized Steel Str Tap Range	7/32 in- 3/4 in
Conductor Type	<ul style="list-style-type: none"><li>• AL C Str-Run</li><li>• CU C Str-Run</li><li>• AAAC C 5005-Run</li><li>• AAAC C 6201-Run</li><li>• ACSR C Str-Run</li><li>• CU C Solid-Run</li><li>• AL C Str-Tap</li><li>• CU C Str-Tap</li><li>• AAAC C 5005-Tap</li><li>• AAAC C 6201-Tap</li><li>• ACSR C Str-Tap</li><li>• CU C Solid-Tap</li><li>• GAL Steel C Str-Size</li></ul>

## Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	EX
Status	
UL Listed	No

## Logistics

Minimum Pack Quantity	1
-----------------------	---

## Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Product Cross Section Image\(s\) - BUR\\_KVSU\\_LineArt](#)  
[Sales Drawings - sd054222-01](#)  
[Specifications - KVSU34G3](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
BRDY-KVSU34G3-SPEC-EN | REV 8/2024