



## KVSW44, Mechanical Connector with Spacer Bar

By Burndy  
Catalog # [KVSW44](#)

Mechanical Connector For CUWeld and Copper Supplied with a CU alloy Spacer that separates run and tap conductors, Run: 500-1000 Kcmil, Tap: 250-1000 Kcmil.



### Application

For Copper And Copperweld Conductors

### General

Catalog Number	KVSW44
EU RoHS Indicator	Yes
Installation Torque	660 LBS/in
Recommended in-lb	
Material	Copper
Plated	N
Plating Type	Unplated
Sub Brand	OKLIP
Trade Name	OKLIP™
Type	KVSW
UPC	781810068052
UPC 12 Digit	7818100680522

### Dimensions

Dimension - Height inch	4.14 in
Dimension - Length Overall inch	1.04 in
Dimension - Stud Size inch	5/8 in
Dimension - Width inch	1.56 in

### Conductor Related

Conductor - Copper Str Run	500 kcmil;550 kcmil;600 kcmil;700 kcmil;750 kcmil;800 kcmil;850 kcmil;900 kcmil;1000 kcmil
Conductor - Copper Str Run Range	500 kcmil- 1000 kcmil
Conductor - Copper Str Tap	250 kcmil;300 kcmil;350 kcmil;400 kcmil;450 kcmil;500 kcmil;550 kcmil;600 kcmil;700 kcmil;750 kcmil;800 kcmil;850 kcmil;900 kcmil;1000 kcmil
Conductor - Copper Str Tap Range	250 kcmil - 1000 kcmil
Conductor Type	CU C Str-Size

### Certifications And Compliance

Buy American Compliant	No
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

### Logistics

Minimum Pack Quantity	1
-----------------------	---

### Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Catalogs - BURNDY Master Catalog - Section A - Mechanical](#)  
[Customer Notices - Prop 65 Notice](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Product Cross Section Image\(s\) - BUR\\_KVSW\\_LineArt](#)  
[Sales Drawings - sd009323-01](#)  
[Specifications - KVSW44](#)

