



KVSW44TN, Mechanical Connector with Spacer Bar

By Burndy
Catalog # [KVSW44TN](#)

Mechanical Connector For CUWeld and Copper Supplied with a CU alloy Spacer that separates run and tap conductors, Run: 500-1000 Kcmil, Tap: 250-1000 Kcmil.



General

Material	Copper
Plated	Y
Plating Type	Tin
Trade Name	OKLIP™
UPC	781810245934
UPC 12 Digit	7818102459344

Dimensions

Dimension - Height inch	4.14 in
Dimension - Length Overall inch	1.04 in
Dimension - Stud Size inch	5/8 in
Dimension - Width inch	1.56 in

Conductor Related

Conductor - Copper Str Run Range	500 kcmil- 1000 kcmil
Conductor - Copper Str Tap Range	250 kcmil - 1000 kcmil
Conductor Type	CU C Str-Size

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - sd009323-01](#)



A proud member of the Hubbell Family.