



LSC5561, AL Lightning Shield Clamp Assembly, 4/0 STR-556 AAC, 5.9 IN L, Galvanized Steel 3/8"-16 Eyebolt, insulation dia:1.34"

By Burndy
Catalog # LSC5561

Cast Al Alloy Lightning Shield Clamp Assembly, 4/0 STR-556 AAC, 5.9 IN L, Galvanized Steel 3/8"-16 Eyebolt,insulation dia:1.34".



Application

For Aluminum And ACSR Primary Covered Conductor (Tree Wire)

General

Catalog Number	LSC5561
EU RoHS Indicator	Yes
Material	Aluminum Alloy
Material - Hardware	Galvanized Steel
Oxide Inhibitor Type	Penetrox A-13
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Sub Brand	CONNECTOR
Type	Arc Protection Device
UPC	781810084960

Dimensions

Dimension - B Length fraction	1-1/2 in
Dimension - B Length inch	1.5 in
Dimension - L Length Overall mm	150 mm
Dimension - Length Overall inch	5.90 in

Conductor Related

Conductor - AL Str Size	4/0 AWG;250 kcmil;266 kcmil;300 kcmil;336 kcmil;350 kcmil;397 kcmil;400 kcmil;450 kcmil;477 kcmil;500 kcmil;550 kcmil;556 kcmil
Conductor - AL Str Size Range	4/0 AWG-556 kcmil

Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	No
Standards - RoHS Compliance Status	CM

Logistics

Minimum Pack Quantity	40
-----------------------	----

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section H - Overhead Distribution](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - SC..091818-01](#)
- [Specifications - LSC5561](#)