



LYM25C, , MOLIMITER Replaceable Link, With DURICOMP™ Shell and Rubber Sleeve for Insulated Cables.

By Burndy
Catalog # [LYM25C](#)



With DURICOMP™ Shell and Rubber Sleeve for Insulated Cables.

General

Catalog Number	LYM25C
Connector Type	Limiter
Die Index	99
Insulation	Y
Insulation Type	Diatex
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	MOLIMITER™
UPC	781810000731
UPC 12 Digit	7818100007311

Dimensions

Dimension - B Length fraction	3/4 in
Dimension - B Length inch	.75 in
Dimension - Length Overall inch	14.25 in

Conductor Related

Conductor - AL Str Size	1/0 AWG
Conductor - AL Str Size Range	1/0 AWG
Conductor - Copper Str Size	1/0 AWG
Conductor - Copper Str Size Range	1/0 AWG

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	UI
UL Listed	No

Logistics

Carton Quantity	4
Minimum Pack Quantity	1
Pallet Quantity	384

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section K - Underground](#)
- [Customer Notices - Prop 65 Notice](#)
- [Installation Manuals - BUR_50073123_Installation_Instructions](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - SD027539-01](#)
- [SDS - DURICOMP SDS](#)
- [Specifications - LYM25C](#)