

## LYM31C, MOLIMITER Replaceable Link

By Burndy  
Catalog # [LYM31C](#)



WIRE: 350kcmil.

### General

Catalog Number	LYM31C
Connector Type	Limiter
Die Index	18
Insulation	Y
Insulation Type	Diatex
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	MOLIMITER™
UPC	781810000793
UPC 12 Digit	7818100007933

### Dimensions

Dimension - B Length fraction	1-1/4 in
Dimension - B Length inch	1.25 in
Dimension - Length Overall inch	14.25 in

### Conductor Related

Conductor - AL Str Size	350 kcmil
Conductor - AL Str Size Range	350 kcmil
Conductor - Copper Str Size	350 kcmil
Conductor - Copper Str Size Range	350 kcmil

### Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	UI
UL Listed	No

### Logistics

Carton Quantity	4
Minimum Pack Quantity	1
Pallet Quantity	384

### Product Assets

[Catalogs - BURNDY Master Catalog - Section K - Underground](#)  
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Installation Manuals - BUR\\_50073123\\_Installation\\_Instructions](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Sales Drawings - SD027539-01](#)  
[Specifications - LYM31C](#)