

## LYM34C, Replaceable Link Limiter - Cable To Mole

By Burndy  
Catalog # [LYM34C](#)



Molimiter Replaceable Link, 500 KCMIL, Tin Plated, 20 Index.

### General

Catalog Number	LYM34C
Connector Type	Limiter
Die Index	20
Feature - Barrel Style	Tapered
Insulation	Y
Material	Copper Alloy
Plated	Y
Plating Type	Tin
Trade Name	MOLIMITER™
UPC	781810000809
UPC 12 Digit	7818100008099

### Dimensions

Dimension - B Length fraction	1-1/4 in
Dimension - B Length inch	1.25 in
Dimension - Length Overall inch	14.25 in

### Conductor Related

Conductor - AL Str Size	500 kcmil
Conductor - AL Str Size Range	500 kcmil
Conductor - Copper Str Size	500 kcmil
Conductor - Copper Str Size Range	500 kcmil

### Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

### Logistics

Carton Quantity	6
Minimum Pack Quantity	12
Pallet Quantity	576

### Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Catalogs - BURNDY Master Catalog - Section K - Underground](#)  
[Customer Notices - Prop 65 Notice](#)  
[Installation Manuals - BUR\\_50073123\\_Installation\\_Instructions](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Product Cross Section Image\(s\) - BUR\\_LYM\\_LineArt](#)  
[Sales Drawings - SD027539-01](#)  
[SDS - DURICOMP SDS](#)  
[Specifications - LYM34C](#)