

# LYS29C, Replaceable Link Limiter - Cable To Cable

By Burndy  
Catalog # [LYS29C](#)



Limiter Replaceable Link, 250 KCMIL, Tin plated, 16 Index.

## Features

- Type LYS Replaceable Link Limiter incorporates the functions of both fuse and coupler
- For use with rubber and paper-insulated cable, it is designed to facilitate rapid replacement of Limiter Links upon clearing

## General

Catalog Number	LYS29C
Connector Type	Limiter
Die Index	16
Feature - Barrel Style	Tapered
Insulation	Y
Insulation Type	Rubber
Plated	Y
Plating Type	Tin - Electro Plated
UPC	781810000779
UPC 12 Digit	7818100007799

## Dimensions

Dimension - B Length fraction	1 in
Dimension - B Length inch	1.00 in
Dimension - Length Overall inch	16.25 in

## Conductor Related

Conductor - AL Str Size	250 kcmil
Conductor - AL Str Size Range	250 kcmil

Conductor - Copper Str Size	250 kcmil
Conductor - Copper Str Size Range	250 kcmil

## Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	EX
Status	
UL Listed	No

## Logistics

Carton Quantity	4
Minimum Pack Quantity	1
Pallet Quantity	384

## Product Assets

- [Catalogs - BURNDY Master Catalog - Section K - Underground](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Installation Manuals - BUR\\_50075049\\_Installation\\_Instructions](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR\\_LYS29C\\_LineArt](#)
- [Sales Drawings - SD020600-01](#)
- [SDS - DURICOMP SDS](#)
- [Specifications - LYS29C](#)