

LYS31C, Replaceable Link Limiter - Cable To Cable

By Burndy
Catalog # LYS31C



Limiter Replaceable Link, 350 KCMIL, Tin plated, 18 Index.

General

Catalog Number	LYS31C
Connector Type	Limiter
Die Index	18
Feature - Barrel Style	Tapered
Insulation	Y
Insulation Type	Rubber
Plated	Y
Plating Type	Tin - Electro Plated
UPC	781810000823
UPC 12 Digit	7818100008233

Dimensions

Dimension - B Length fraction	1-1/4 in
Dimension - B Length inch	1.25 in
Dimension - Length Overall inch	16.25 in

Conductor Related

Conductor - AL Str Size	350 kcmil
Conductor - AL Str Size Range	350 kcmil
Conductor - Copper Str Size	350 kcmil
Conductor - Copper Str Size Range	350 kcmil

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Carton Quantity	6
Minimum Pack Quantity	1
Pallet Quantity	540

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Catalogs - BURNDY Master Catalog - Section K - Underground](#)
[Customer Notices - Prop 65 Notice](#)
[Installation Manuals - BUR_50075049_Installation_Instructions](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_LYS29C_LineArt](#)
[Sales Drawings - SD020600-01](#)
[SDS - DURICOMP SDS](#)
[Specifications - LYS31C](#)