

## LYS34C, Replaceable Link Limiter - Cable To Cable

By Burndy  
Catalog # [LYS34C](#)



Replaceable Link limiter with DURICOMP shell and Rubber Sleeve , 500 kcmil, 20 Index.

### General

Catalog Number	LYS34C
Connector Type	Limiter
Die Index	20
Feature - Barrel Style	Tapered
Insulation	Y
Insulation Type	Rubber
Plated	Y
Plating Type	Tin
UPC	781810000830
UPC 12 Digit	7818100008300

### Dimensions

Dimension - B Length fraction	1-1/4 in
Dimension - B Length inch	1.25 in
Dimension - Length Overall inch	16.25 in

### Conductor Related

Conductor - AL Str Size	500 kcmil
Conductor - AL Str Size Range	500 kcmil
Conductor - Copper Str Size	500 kcmil
Conductor - Copper Str Size Range	500 kcmil

### Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	EX
Status	
UL Listed	No

### Logistics

Carton Quantity	4
Minimum Pack Quantity	2
Pallet Quantity	288

### Product Assets

- [3D Models - LYS34C\\_MODEL-PDF](#)
- [3D Models - LYS34C\\_MODEL-STEP](#)
- [3D Models - LYS34C\\_MODEL-IGES](#)
- [Catalogs - BURNDY Master Catalog - Section K - Underground](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Installation Manuals - BUR\\_50075049\\_Installation\\_Instructions](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR\\_LYS29C\\_LineArt](#)
- [Sales Drawings - SD020600-01](#)
- [SDS - DURICOMP SDS](#)
- [Specifications - LYS34C](#)